



Technical Data Sheet

DOW™ LLDPE DFDC-7047 NT 7 Linear Low Density Polyethylene

Overview

DOW™ DFDC-7047 NT7 Linear Low Density Polyethylene is an ethylene-butene copolymer designed for blown film applications. This resin is formulated with an additive package that does not contain any intentionally added TNPP (TrisnonylphenylPhosphite).

Main Characteristics

- Butene linear low density polyethylene
- Blown film extrusion
- Pellet form
- Non-TNPP (Tris(nonylphenyl) phosphite) based formulation

Complies with

- EU, No 10/2011
- U.S. FDA, 21 CFR 177.1520(c)3.2a

Consult the regulations for complete details.

Typical Properties¹

Physical	Nominal Value (SI)	Unit	Test Method ²
Density	0.918	g/cm ³	ASTM D792
Melt Mass-Flow Rate (MFR) (230°C/2.16 kg)	1.0	g/10 min	ASTM D1238
Films			
Film Thickness-Tested	25	μm	Internal Method
Film Puncture Energy	2.49	J	Internal Method
Film Puncture Force	35.6	N	Internal Method
Film Puncture Resistance	12.0	J/cm ³	ASTM D882
Film Toughness - MD	96.8	J/cm ³	ASTM D882
Film Toughness - TD	95.1	J/cm ³	ASTM D882
Secant Modulus			
1% Secant, MD	221	MPa	ASTM D882
2% Secant, MD	189	MPa	
1% Secant, TD	248	MPa	
2% Secant, TD	210	MPa	ASTM D882
Tensile Strength - MD (Yield)	10.7	MPa	
Tensile Strength - TD (Yield)	11.0	MPa	

1. These are typical properties only and are not to be construed as specifications. Users should confirm results by their own tests.
2. ASTM: American Society for Testing and Materials



Typical Properties (Cont.)

Films	Nominal Value (SI)	Unit	Test Method
Tensile Strength - MD (Break)	36.5	MPa	ASTM D882
Tensile Strength - TD (Break)	26.9	MPa	ASTM D882
Tensile Elongation - MD (Break)	580	%	ASTM D882
Tensile Elongation - TD (Break)	690	%	ASTM D882
Dart Drop Impact	90	g	ASTM D1709A
Elmendorf Tear Strength - MD ³	170	g	ASTM D1922
Elmendorf Tear Strength - TD ³	320	g	ASTM D1922
Thermal			
Melting Temperature	121	°C	ISO ⁴ 3146
Vicat Softening Temperature	102	°C	ASTM D1525
Optical			
Gloss (45°)	33		ASTM D2457
Haze	19.0	%	ASTM D1003

3. Method B
4. ISO: International Standardization Organization

Extrusion Notes

Fabrication Conditions for Blown Film:

- Screw Size: 3.5in.; 30:1ratio L/D
- Screw Type: DSB II
- Die Gap: 70 mil (1.8 mm)
- Melt Temperature: 420°F
- Output: 12 lb/hr/in. of die circumference
- Die Diameter: 8 in.
- Blow-Up Ratio: 2.5 to 1
- Screw Speed: 39 rpm
- Frost Line Height: 51 in.

Product Stewardship

The Dow Chemical Company and its subsidiaries ("Dow") has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our Product Stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our Product Stewardship program rests with each and every individual involved with Dow products — from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

Dow strongly encourages its customers to review both their manufacturing processes and their applications of Dow products from the standpoint of human health and environmental quality to ensure that Dow products are not used in ways for which they are not intended or tested. Dow personnel are available to answer your questions and to provide reasonable technical support. Dow product literature, including safety data sheets, should be consulted prior to use of Dow products. Current safety data sheets are available from Dow.



Medical Applications Policy

NOTICE REGARDING MEDICAL APPLICATION RESTRICTIONS: Dow will not knowingly sell or sample any product or service ("Product") into any commercial or developmental application that is intended for:

- long-term or permanent contact with internal bodily fluids or tissues. "Long-term" is contact which exceeds 72 continuous hours;
- use in cardiac prosthetic devices regardless of the length of time involved ("cardiac prosthetic devices" include, but are not limited to, pacemaker leads and devices, artificial hearts, heart valves, intra-aortic balloons and control systems, and ventricular bypass-assisted devices);
- use as a critical component in medical devices that support or sustain human life; or
- use specifically by pregnant women or in applications designed specifically to promote or interfere with human reproduction.

Dow requests that customers considering use of Dow products in medical applications notify Dow so that appropriate assessments may be conducted. Dow does not endorse or claim suitability of its products for specific medical applications. It is the responsibility of the medical device or pharmaceutical manufacturer to determine that the Dow product is safe, lawful, and technically suitable for the intended use. **DOW MAKES NO WARRANTIES, EXPRESS OR IMPLIED, CONCERNING THE SUITABILITY OF ANY DOW PRODUCT FOR USE IN MEDICAL APPLICATIONS.**

