



Technical Data Sheet

ELITE™ AT 6502B Enhanced Polyethylene Resin

Description

ELITE™ AT 6502B Enhanced Polyethylene Resin is an enhanced LLDPE ethylene-octene copolymer from Dow. It offers a unique combination of low seal initiation temperature, high hot tack strength, high impact resistance, good optical properties and it is easy to process.

Sustainability Attribute:



Main Characteristics

- Low seal initiation temperature and broad hot tack window
- High hot tack strength
- High impact and puncture resistance, as well as good tear properties
- Good optical properties
- High throughput resin with excellent bubble stability

Complies with:

- U.S. FDA FCN 424
- Canadian HPFB No Objection

Consult the regulations for complete details.

Additives

- Antiblock: Yes
- Slip: Yes
- Processing aid: No

Properties¹

Physical	Nominal Value	Unit (English)	Nominal Value	Unit (SI)	Test Method ²
Density	0.916	g/cm ³	0.916	g/cm ³	ASTM D792
Base Density ³	0.914	g/cm ³	0.914	g/cm ³	Dow Method
Melt Index (190°C/2.16 kg)	0.85	g/10 min	0.85	g/10 min	ASTM D1238
Films					
Film Thickness – Tested	2	mil	50	µm	
Film Puncture Energy to Break	37.2	in·lb	4.2	J	
Film Puncture Resistance	123.3	ft·lb/in ³	10.2	J/cm ³	
Secant Modulus					ASTM D882
2% Secant, MD	57000	psi	393	MPa	
2% Secant, TD	57870	psi	399	MPa	

1. These are typical properties only and are not to be construed as specifications. Users should confirm results by their own tests.
2. ASTM: American Society for Testing and Materials
3. Base density is estimated using the assumption that every 1000 ppm of antiblock in the finished product raises the density of the polymer by 0.0006 g/cm³. Base density is the estimated density of the polymer if it did not contain any antiblock.



Properties (Cont.)

Films	Nominal Value	Unit (English)	Nominal Value	Unit (SI)	Test Method
Tensile Strength					ASTM D882
MD : Yield	2610	psi	18.0	MPa	
TD : Yield	2538	psi	17.5	MPa	
MD : Break	7962	psi	54.9	MPa	
TD : Break	7628	psi	52.6	MPa	
Tensile Elongation					ASTM D882
MD : Break	471	%	471	%	
TD : Break	491	%	491	%	
Dart Drop Impact	1815	g	1815	g	ASTM D1709A
Thermal					
Melting Temperature (DSC)	246	°F	119	°C	Dow Method
Optical					
Gloss (45°)	48		48		ASTM D2457
Haze	16.5	%	16.5	%	ASTM D1003

Extrusion Notes

Fabrication Conditions:

- Die Diameter: 200 mm
- Die Gap: 1.8 mm
- Melt Temperature: 230°C
- Output: 50 kg/h
- Blow-Up Ratio: 2.5 to 1
- Screw Speed: 40 rpm
- Frost Line height: 500 mm

Product Stewardship

The Dow Chemical Company and its subsidiaries ("Dow") has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our Product Stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our Product Stewardship program rests with each and every individual involved with Dow products — from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice

Dow strongly encourages its customers to review both their manufacturing processes and their applications of Dow products from the standpoint of human health and environmental quality to ensure that Dow products are not used in ways for which they are not intended or tested. Dow personnel are available to answer your questions and to provide reasonable technical support. Dow product literature, including safety data sheets, should be consulted prior to use of Dow products. Current safety data sheets are available from Dow.



Medical Applications Policy

NOTICE REGARDING MEDICAL APPLICATION RESTRICTIONS: Dow will not knowingly sell or sample any product or service ("Product") into any commercial or developmental application that is intended for:

- long-term or permanent contact with internal bodily fluids or tissues. "Long-term" is contact which exceeds 72 continuous hours;
- use in cardiac prosthetic devices regardless of the length of time involved ("cardiac prosthetic devices" include, but are not limited to, pacemaker leads and devices, artificial hearts, heart valves, intra-aortic balloons and control systems, and ventricular bypass-assisted devices);
- use as a critical component in medical devices that support or sustain human life; or
- use specifically by pregnant women or in applications designed specifically to promote or interfere with human reproduction.

Dow requests that customers considering use of Dow products in medical applications notify Dow so that appropriate assessments may be conducted. Dow does not endorse or claim suitability of its products for specific medical applications. It is the responsibility of the medical device or pharmaceutical manufacturer to determine that the Dow product is safe, lawful, and technically suitable for the intended use. **DOW MAKES NO WARRANTIES, EXPRESS OR IMPLIED, CONCERNING THE SUITABILITY OF ANY DOW PRODUCT FOR USE IN MEDICAL APPLICATIONS.**

